

Fixed castors

Item description/product images



Description

Material:

Housing, steel plate.

Wheel tread, high quality polyurethane elastomere.

Wheel rims, die-cast aluminium.

Version:

Housing, press-formed.

Swivel housing, double-row ball bearings in a swivel head.

Ball bearing wheel axle bearings.

Note:

Wheel axle bolted.

Swivel and fixed castors with mounting plate.

Application:


Heavy loads can be easily transported using this load handling equipment. The roll and swivel resistance is reduced with this new wheel series designed for intralogistic heavy load applications.

Temperature range:

-25 °C to +70 °C

Drawings

fixed castor



Fixed castors

Overview of items

Order No.	Item	Wheel bearing	B	B1	B2	B3	D	D1	H	L	L1	L2	Permissible load kg
K1788.1010004011	Fixed castor	ball bearing	40	60	55	85	100	9	130	100	80	76	350
K1788.1010004013	Fixed castor	ball bearing	40	80	75	110	100	11	130	140	105	-	350
K1788.1012504011	Fixed castor	ball bearing	40	60	55	85	125	9	155	100	80	76	350
K1788.1012504013	Fixed castor	ball bearing	40	80	75	110	125	11	155	140	105	-	350
K1788.101500501	Fixed castor	ball bearing	50	80	75	110	150	11	197	140	105	-	500
K1788.101600501	Fixed castor	ball bearing	50	80	75	110	160	11	202	140	105	-	550
K1788.102000501	Fixed castor	ball bearing	50	80	75	110	200	11	245	140	105	-	600