

## Latches adjustable, fastening holes accessible, Form B



#### Item description/product images



#### **Description**

#### Material:

Steel or stainless steel 1.4301.

#### **Version:**

Steel trivalent blue passivated. Stainless steel bright.

#### Note:

Adjustable latches are secure locking systems for industrial applications. By exceeding the dead centre they resist vibration.

After the hook is engaged with the catch plate, the parts to be locked can be drawn together by up to 5 mm by pushing the lever down.

To compensate for tolerances or to create enough tension, the hook length can be adjusted using the M5 threaded spindle.

The latches can be screwed down or riveted.

Any catch plate can be combined with any latch.

Order required catch plate version separately.

The retaining force F1 applies to the latch, not the catch plate.

#### **Drawing reference:**


Form B with lock





# Latches adjustable, fastening holes accessible, Form B




### **Drawings**









#### **Overview of items**

### Latches adjustable, fastening holes accessible

Order No.	Main	Form	Retaining
	material		force
			F1 N
K0046.2420721	steel	В	1000
K0046.2420722	stainless steel	В	1000