



Impressive advantages:

- Repeat accuracy ≤ 0.01 mm
- Fixed jaw fixed in all directions (X,Y,Z)
- Wide clamping range due to use of attachment step jaws
- Basic equipment: 2 rotating screw-in jaws and 1 crank handle
- Can be inclined sideways, with fastening holes for slot spacing of 63 mm and 100 mm.