

# Ball-end thrust screws without head stainless steel with flattened ball and rotation lock

Item description/product images



## Description

### Material:

Screw and ball stainless steel.

### Version:


Stainless steel bright.

### Note:

Surfaces which are not flat and parallel can be firmly clamped or supported with a flattened ball, the movable ball can adapt itself up to 9°.

Longer versions have been designed especially to be glued in. This enables mechanical connecting elements with external thread to be made cost-effectively for small and medium-sized series.

## Drawings



## Overview of items

Order No.	Form	D	D1	L	Ball-Ø	SW	Load rating max. kN (static load only)
K0384.50612	BV	M6	3	12,1	4	3	6
K0384.50616	BV	M6	3	16,1	4	3	6
K0384.50620	BV	M6	3	20,1	4	3	6
K0384.50625	BV	M6	3	25,1	4	3	6
K0384.50816	BV	M8	4,1	16,3	5,5	4	9
K0384.50820	BV	M8	4,1	20,3	5,5	4	9
K0384.50825	BV	M8	4,1	25,3	5,5	4	9
K0384.50830	BV	M8	4,1	30,3	5,5	4	9
K0384.51020	BV	M10	5,6	20,3	7	5	12
K0384.51025	BV	M10	5,6	25,3	7	5	12
K0384.51035	BV	M10	5,6	35,3	7	5	12
K0384.51040	BV	M10	5,6	40,2	7	5	12
K0384.51220	BV	M12	7	20,2	8,5	6	18
K0384.51230	BV	M12	7	30,2	8,5	6	18
K0384.51240	BV	M12	7	40,2	8,5	6	18
K0384.51250	BV	M12	7	50	8,5	6	18
K0384.51635	BV	M16	10,7	35	12	8	36
K0384.51650	BV	M16	10,7	50	12	8	36

**Ball-end thrust screws without head stainless steel with flattened ball  
and rotation lock**

