

Fixed castors

Item description/product images



Description

Material:

Housing sheet steel,

Wheels high quality elastic solid rubber.

Wheel rim high-quality unbreakable polyamide (wheel Ø 100 and 125 mm) or die-cast aluminium (wheel Ø from 150 mm).

Version:

Housing, press-formed.

Swivel housing, double-row ball bearings in a swivel head.

Ball bearing wheel axle bearings.

Note:

Wheel axle bolted.

Swivel and fixed castors with mounting plate.

Application:


Maximum travel comfort, excellent cushioning of the transported goods. The new soft rubber series brings noticeable noise reduction in all applications.

Temperature range:

-25 °C to +80 °C.

Drawings

fixed castor



Fixed castors

Overview of items

Order No.	Item	Wheel bearing	B	B1	B2	B3	D	D1	H	L	L1	L2	Permissible load kg
K1766.101000401	Fixed castor	ball bearing	40	60	55	85	100	9	125	100	80	76	150
K1766.101250401	Fixed castor	ball bearing	40	60	55	85	125	9	150	100	80	76	150
K1766.101500401	Fixed castor	ball bearing	40	80	75	110	150	11	190	140	105	-	280
K1766.101600501	Fixed castor	ball bearing	50	80	75	110	160	11	195	140	105	-	300
K1766.102000501	Fixed castor	ball bearing	50	80	75	110	200	11	235	140	105	-	300