

Magnets raw, Form A with countersink hole, NdFeB, disc form

Item description/product images



Description

Material:
NdFeB (neodymium).

Version:
Electro zinc-plated.


Note:
Unshielded system.

Temperature range:
max. 80°C.

Assembly:
The magnets can be mounted by press-fit, screwing-in or gluing.

Drawing reference:
1) magnetic face

Drawings



Overview of items

Order No.	Form	D	D1	H	Tightening torque max. Nm	Magnetic force N
K1405.12	A	12 ±0,1	3,5 ±0,1	3 ±0,1	3	18
K1405.15	A	15 ±0,1	4,5 ±0,1	3,5 ±0,1	3	29
K1405.18	A	18 ±0,1	4,5 ±0,1	4 ±0,1	3	41
K1405.24	A	24 ±0,1	5,5 ±0,1	4 ±0,1	3	66