

## Slotted round nuts DIN 1804

### Item description/product images



### Description

#### Material:

Mild steel.

Stainless steel A2.

#### Version:


Form W = black oxidised.

Form H = hardened and ground both sides.

#### Note:

Form H is case hardened, apart from the thread.

### Drawings



### Overview of items

#### Slotted round nuts DIN 1804

| Order No. | Form | Main material | Slot width B<br>DIN 650 | D1      | D2 | D3 | H  | H1  | T   |
|-----------|------|---------------|-------------------------|---------|----|----|----|-----|-----|
| K1917.110 | W    | mild steel    | 5                       | M10x1   | 25 | 20 | 6  | 0,5 | 2   |
| K1917.112 | W    | mild steel    | 5                       | M12x1,5 | 28 | 23 | 6  | 0,5 | 2   |
| K1917.114 | W    | mild steel    | 5                       | M14x1,5 | 30 | 25 | 7  | 0,5 | 2   |
| K1917.116 | W    | mild steel    | 5                       | M16x1,5 | 32 | 27 | 7  | 0,5 | 2   |
| K1917.118 | W    | mild steel    | 6                       | M18x1,5 | 34 | 28 | 8  | 0,5 | 2,5 |
| K1917.120 | W    | mild steel    | 6                       | M20x1,5 | 36 | 30 | 8  | 0,5 | 2,5 |
| K1917.122 | W    | mild steel    | 6                       | M22x1,5 | 40 | 34 | 9  | 0,5 | 2,5 |
| K1917.124 | W    | mild steel    | 6                       | M24x1,5 | 42 | 36 | 9  | 0,5 | 2,5 |
| K1917.126 | W    | mild steel    | 7                       | M26x1,5 | 45 | 38 | 10 | 0,5 | 3   |
| K1917.128 | W    | mild steel    | 7                       | M28x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.130 | W    | mild steel    | 7                       | M30x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.132 | W    | mild steel    | 7                       | M32x1,5 | 52 | 45 | 11 | 0,5 | 3   |
| K1917.135 | W    | mild steel    | 7                       | M35x1,5 | 55 | 48 | 11 | 0,5 | 3   |
| K1917.138 | W    | mild steel    | 8                       | M38x1,5 | 58 | 50 | 11 | 0,5 | 3,5 |
| K1917.140 | W    | mild steel    | 8                       | M40x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |
| K1917.142 | W    | mild steel    | 8                       | M42x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |
| K1917.210 | H    | mild steel    | 5                       | M10x1   | 25 | 20 | 6  | 0,5 | 2   |
| K1917.212 | H    | mild steel    | 5                       | M12x1,5 | 28 | 23 | 6  | 0,5 | 2   |
| K1917.214 | H    | mild steel    | 5                       | M14x1,5 | 30 | 25 | 7  | 0,5 | 2   |
| K1917.216 | H    | mild steel    | 5                       | M16x1,5 | 32 | 27 | 7  | 0,5 | 2   |

## Slotted round nuts DIN 1804

### Overview of items

| Order No. | Form | Main material      | Slot width B<br>DIN 650 | D1      | D2 | D3 | H  | H1  | T   |
|-----------|------|--------------------|-------------------------|---------|----|----|----|-----|-----|
| K1917.218 | H    | mild steel         | 6                       | M18x1,5 | 34 | 28 | 8  | 0,5 | 2,5 |
| K1917.220 | H    | mild steel         | 6                       | M20x1,5 | 36 | 30 | 8  | 0,5 | 2,5 |
| K1917.222 | H    | mild steel         | 6                       | M22x1,5 | 40 | 34 | 9  | 0,5 | 2,5 |
| K1917.224 | H    | mild steel         | 6                       | M24x1,5 | 42 | 36 | 9  | 0,5 | 2,5 |
| K1917.226 | H    | mild steel         | 7                       | M26x1,5 | 45 | 38 | 10 | 0,5 | 3   |
| K1917.228 | H    | mild steel         | 7                       | M28x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.230 | H    | mild steel         | 7                       | M30x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.232 | H    | mild steel         | 7                       | M32x1,5 | 52 | 45 | 11 | 0,5 | 3   |
| K1917.235 | H    | mild steel         | 7                       | M35x1,5 | 55 | 48 | 11 | 0,5 | 3   |
| K1917.238 | H    | mild steel         | 8                       | M38x1,5 | 58 | 50 | 11 | 0,5 | 3,5 |
| K1917.240 | H    | mild steel         | 8                       | M40x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |
| K1917.242 | H    | mild steel         | 8                       | M42x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |
| K1917.310 | -    | stainless steel A2 | 5                       | M10x1   | 25 | 20 | 6  | 0,5 | 2   |
| K1917.312 | -    | stainless steel A2 | 5                       | M12x1,5 | 28 | 23 | 6  | 0,5 | 2   |
| K1917.314 | -    | stainless steel A2 | 5                       | M14x1,5 | 30 | 25 | 7  | 0,5 | 2   |
| K1917.316 | -    | stainless steel A2 | 5                       | M16x1,5 | 32 | 27 | 7  | 0,5 | 2   |
| K1917.318 | -    | stainless steel A2 | 6                       | M18x1,5 | 34 | 28 | 8  | 0,5 | 2,5 |
| K1917.320 | -    | stainless steel A2 | 6                       | M20x1,5 | 36 | 30 | 8  | 0,5 | 2,5 |
| K1917.322 | -    | stainless steel A2 | 6                       | M22x1,5 | 40 | 34 | 9  | 0,5 | 2,5 |
| K1917.324 | -    | stainless steel A2 | 6                       | M24x1,5 | 42 | 36 | 9  | 0,5 | 2,5 |
| K1917.326 | -    | stainless steel A2 | 7                       | M26x1,5 | 45 | 38 | 10 | 0,5 | 3   |
| K1917.328 | -    | stainless steel A2 | 7                       | M28x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.330 | -    | stainless steel A2 | 7                       | M30x1,5 | 50 | 43 | 10 | 0,5 | 3   |
| K1917.332 | -    | stainless steel A2 | 7                       | M32x1,5 | 52 | 45 | 11 | 0,5 | 3   |
| K1917.335 | -    | stainless steel A2 | 7                       | M35x1,5 | 55 | 48 | 11 | 0,5 | 3   |
| K1917.338 | -    | stainless steel A2 | 8                       | M38x1,5 | 58 | 50 | 11 | 0,5 | 3,5 |
| K1917.340 | -    | stainless steel A2 | 8                       | M40x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |
| K1917.342 | -    | stainless steel A2 | 8                       | M42x1,5 | 62 | 54 | 12 | 0,5 | 3,5 |