

# Indexing plungers, steel or stainless steel with status sensor, plastic mushroom grip and locking slot

Item description/product images



## Description

### Material:

Steel version:

Threaded sleeve and indexing pin free-cutting steel.

Stainless-steel version:

Indexing pin hardened:

Threaded sleeve 1.4305.

Indexing pin 1.4034.

Indexing pin not hardened:

Threaded sleeve 1.4305.

Indexing pin 1.4305.

Mushroom knob and cover thermoplastic.

### Version:

Steel version:

Threaded sleeve, black oxidised.

Indexing pin hardened, ground and black oxidised.

Stainless-steel version:

Threaded sleeve bright.

Indexing pin hardened, ground and bright.

Indexing pin not hardened, ground and bright.

Mushroom knob dark grey.

Cover translucent grey.

### Application:

Indexing plungers with status sensor allow actuation-dependent process control. It is also possible to ensure that the indexing pin is in the desired actuation status.

### Advantages:

Wireless transfer of actuation status.

Laborious cable connections no longer necessary.

Intelligent battery management allows long running time

No interfering edges.

### Accessory:


K1494 Gateway

### Safety:

Indexing plungers with status sensor are not suitable for personnel safety functions.

## Indexing plungers, steel or stainless steel with status sensor, plastic mushroom grip and locking slot

Drawings



### Overview of items

Order No.	Form	Main material	Surface finish body	D	D1	D2	Travel S	L	L1	L2	L3	SW1	Fx30°	Travel S	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1495.3105	C	steel	hardened	5	M10x1	35	5	57	17	7	15	13	1,3	5	5	12
K1495.3206	C	steel	hardened	6	M12x1,5	35	6	62	20	8	17	14	1,8	6	6	14
K1495.3308	C	steel	hardened	8	M16x1,5	35	8	76	26	10	23	19	2,3	8	15	35
K1495.3410	C	steel	hardened	10	M20x1,5	35	10	82	28	12	25	22	2,8	10	15	34
K1495.3412	C	steel	hardened	12	M20x1,5	35	12	86	28	14	25	22	2,8	12	15	39
K1495.03105	C	stainless steel	hardened	5	M10x1	35	5	57	17	7	15	13	1,3	5	5	12
K1495.03206	C	stainless steel	hardened	6	M12x1,5	35	6	62	20	8	17	14	1,8	6	6	14
K1495.03308	C	stainless steel	hardened	8	M16x1,5	35	8	76	26	10	23	19	2,3	8	15	35
K1495.03410	C	stainless steel	hardened	10	M20x1,5	35	10	82	28	12	25	22	2,8	10	15	34
K1495.03412	C	stainless steel	hardened	12	M20x1,5	35	12	86	28	14	25	22	2,8	12	15	39
K1495.13105	C	stainless steel	not hardened	5	M10x1	35	5	57	17	7	15	13	1,3	5	5	12
K1495.13206	C	stainless steel	not hardened	6	M12x1,5	35	6	62	20	8	17	14	1,8	6	6	14
K1495.13308	C	stainless steel	not hardened	8	M16x1,5	35	8	76	26	10	23	19	2,3	8	15	35
K1495.13410	C	stainless steel	not hardened	10	M20x1,5	35	10	82	28	12	25	22	2,8	10	15	34
K1495.13412	C	stainless steel	not hardened	12	M20x1,5	35	12	86	28	14	25	22	2,8	12	15	39