Levelling feet, steel with hollow screw



Item description/product images





Description

Material:

Plate and hollow screw steel.

Version:

Plate black phosphated or painted yellow. Hollow screw electro zinc-plated or black phosphated.

Note:

These levelling feet are suitable for heavy loads. They are used in particular for large machines and systems, as well as in automation and robotics.

The hollow screw permits the levelling foot to be mounted directly into the floor. The machine can be optimally and precisely aligned via the fine thread.

The load values specified in the table are based on a test series in which a static load was applied perpendicular to the plates through the centre of the spindle. Radially acting forces, such as those produced by vibrations or other shaking effects, affect the load rating and are not taken into account for the specified values.

A maximum inclination of less than 3° can be compensated for.

Supplied as individual components.

Supplied with: Plate K2347. Hollow screw K2346. Nut K2348.

Accessory: Nut K2348.

Levelling feet, steel with hollow screw



Item description/product images





Levelling feet, steel with hollow screw



Drawings



Overview of items

Levelling feet, steel with hollow screw

Order No.	Surface finish body	Surface finish component	Main colour	D	D1	D2 H H1	H2 L	SW	SW1	Load rating max. kN (static load only)
K2345.1111002413X087	painted	galvanised	daffodil yellow RAL 1007	100	M24x2	13 18 120	15 87	24	36	60
K2345.1111203622X100	painted	galvanised	daffodil yellow RAL 1007	120	M36x2	22 25 140	15 10) 41	55	90
K2345.1111503622X100	painted	galvanised	daffodil yellow RAL 1007	150	M36x2	22 25 140	15 10) 41	55	90
K2345.1111503622X177	painted	galvanised	daffodil yellow RAL 1007	150	M36x2	22 25 217	15 17	7 41	55	90
K2345.1211002413X087	phosphated	galvanised	black	100	M24x2	13 18 120	15 87	24	36	60
K2345.1211203622X100	phosphated	galvanised	black	120	M36x2	22 25 140	15 10) 41	55	90
K2345.1211503622X100	phosphated	galvanised	black	150	M36x2	22 25 140	15 10) 41	55	90
K2345.1211503622X177	phosphated	galvanised	black	150	M36x2	22 25 217	15 17	7 41	55	90
K2345.1221002413X087	phosphated	phosphated	black	100	M24x2	13 18 120	15 87	24	36	60
K2345.1221203622X100	phosphated	phosphated	black	120	M36x2	22 25 140	15 10) 41	55	90
K2345.1221503622X100	phosphated	phosphated	black	150	M36x2	22 25 140	15 10) 41	55	90
K2345.1221503622X177	phosphated	phosphated	black	150	M36x2	22 25 217	15 17	7 41	55	90