

Swivel and fixed castors heavy-duty version

Item description/product images



Description

Material:

Housing thick steel plate.

Wheels welded steel body and Extrathane® tread.

Version:

Housing press formed.


Swivel castor housing with strong fork and base plate, very robust centre pin bolted and secured. The swivel head is additionally reinforced with specially formed and hardened bearing shells.

Note:

These castors are particularly shock and impact proof. The treads resist abrasion and are elastic and low-noise. Wheel axle bolted.

Swivel and fixed castors heavy-duty version

Drawings



Overview of items

Swivel and fixed castors heavy-duty version

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
K1768.125501	Fixed castor	without locking system	ball bearing	-	50	80	75	110	125	11	170	140	105	-	500
K1768.160501	Fixed castor	without locking system	ball bearing	-	50	80	75	110	160	11	202	140	105	-	700

Swivel and fixed castors heavy-duty version

Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
K1768.200501	Fixed castor	without locking system	ball bearing	-	50	80	75	110	200	11	245	140	105	-	900
K1768.12550	Swivel castor	without locking system	ball bearing	55	50	80	75	110	125	11	170	140	105	117,5	500
K1768.16050	Swivel castor	without locking system	ball bearing	65	50	80	75	110	160	11	202	140	105	145	700
K1768.20050	Swivel castor	without locking system	ball bearing	70	50	80	75	110	200	11	245	140	105	170	900
K1768.125502	Swivel castor	with stop-top locking system	ball bearing	55	50	80	75	110	125	11	170	140	105	117,5	500
K1768.160502	Swivel castor	with stop-top locking system	ball bearing	65	50	80	75	110	160	11	202	140	105	145	700
K1768.200502	Swivel castor	with stop-top locking system	ball bearing	70	50	80	75	110	200	11	245	140	105	170	900