

Hexagon nuts with thread lock DIN 980 enhanced

Item description/product images



Description

Material:

Steel or stainless steel A2.

Version:

Electro zinc-plated steel.

Bright stainless steel.

Note:

Hexagon nuts with thread lock DIN 980, Form V (all-metal nut, one piece).

The maximum nut height H max. is shown in the table.


The form and dimensions of the stainless steel versions are the same as for DIN 934 with additional crimping.

Drawing reference:

a) Steel

b) Stainless steel

Drawings



Overview of items

Hexagon nuts with thread lock#DIN 980 enhanced

Order No.	Main material	Grade	D	E	H	M	SW
K1146.204	steel	8	M4	7,66	4,2	2,2	7
K1146.205	steel	8	M5	8,79	5,1	2,75	8
K1146.206	steel	8	M6	11,05	6	3,3	10
K1146.208	steel	8	M8	14,38	8	4,4	13
K1146.210	steel	8	M10	18,9	10	5,5	17
K1146.212	steel	8	M12	21,1	12	6,6	19
K1146.214	steel	8	M14	23,9	14	7,7	22
K1146.216	steel	8	M16	26,76	16	8,8	24
K1146.220	steel	8	M20	32,95	20	11	30
K1146.224	steel	8	M24	39,55	24	13,2	36
K1146.227	steel	8	M27	45,2	27	14,8	41
K1146.230	steel	8	M30	50,85	30	16,5	46
K1146.308	steel	10	M8	14,38	8	4,4	13
K1146.310	steel	10	M10	18,9	10	5,5	17
K1146.312	steel	10	M12	21,1	12	6,6	19
K1146.314	steel	10	M14	23,9	14	7,7	22
K1146.316	steel	10	M16	26,76	16	8,8	24
K1146.320	steel	10	M20	32,95	20	11	30
K1146.324	steel	10	M24	35	24	13,2	36
K1146.327	steel	10	M27	45,2	27	14,8	41
K1146.330	steel	10	M30	50,85	30	16,5	46
K1146.104	stainless steel A2	70	M4	7,66	4,2	2,2	7
K1146.105	stainless steel A2	70	M5	8,79	5,1	2,75	8
K1146.106	stainless steel A2	70	M6	11,05	6	3,3	10

Hexagon nuts with thread lock DIN 980 enhanced

Overview of items

Order No.	Main material	Grade	D	E	H	M	SW
K1146.108	stainless steel A2	70	M8	14,38	8	4,4	13
K1146.110	stainless steel A2	70	M10	18,9	10	5,5	17
K1146.112	stainless steel A2	70	M12	21,1	12	6,6	19
K1146.114	stainless steel A2	70	M14	23,9	14	7,7	22
K1146.116	stainless steel A2	70	M16	26,76	16	8,8	24
K1146.120	stainless steel A2	70	M20	32,95	20	11	30
K1146.124	stainless steel A2	70	M24	39,55	24	13,2	36