## 5-axis clamping system for T-slots



### Item description/product images



## Description

#### Note:

5-axis vices for mounting on machine tables with T-slots. These vices enable 5sided machining free of interfering edges with a clamping depth of only 8 mm. With this clamping system, clamping widths of 22–236 mm are possible, and can be extended as desired using the optionally available K0947 extension shafts. By installing a tension spindle immediately under the workpiece support, a force of up to 42 kN is applied to the workpiece, this is not lost due to flexing. The use of clamping pins with a 4 mm cup point allows positive-fit clamping without pre-embossing.

The fastening set K0951 is recommended for mounting the vices on T-slot tables. The set includes one extension shaft with L = 60 mm and one with L = 120 mm.

\* The clamping height can be extended with the riser plates K0941 and seating ledges K0942.

## 5-axis clamping system for T-slots



### Drawings





clamping force 5 axis clamping system



#### **Overview of items**

### 5 Axis clamping system for T-slots

Order No.	Suitable for	А	A1	В	D	Н	Clamping force max. kN	weight kg
K0940.063175	slot spacing 63 - 126	63	126	158	12,5	175 *	42	21,32



# 5-axis clamping system for T-slots

**Overview of items** 

