

Knurled knobs

Item description/product images



Description

Material:

Grip black grey thermoplastic.

Bush brass or stainless steel 1.4305.

Screw steel 5.8 or stainless steel 1.4305.

Version:


Steel trivalent blue passivated.

Stainless steel, bright.

On request:

Other colours.

Drawings



Overview of items

Knurled knobs

Order No.	Thread type	Component material	D	D1	D2	D3	H	H1	T	L
K0110.003	1 pce. prism	560 mm / M10x1.25 / M8	M3	15	11	13	11,5	4,3	4,5	-
K0110.004	1 pce. prism	560 mm / M10x1.25 / M8	M4	15	11	13	11,5	4,3	6	-
K0110.005	1 pce. prism	560 mm / M10x1.25 / M8	M5	15	11	13	11,5	4,3	6	-
K0110.0003	1 pce. prism	22012-25061	M3	15	11	13	11,5	4,3	4,5	-
K0110.0004	1 pce. prism	22012-25061	M4	15	11	13	11,5	4,3	6	-
K0110.0005	1 pce. prism	22012-25061	M5	15	11	13	11,5	4,3	6	-
K0110.003X8	-1.5 - 4.5	0.002	M3	15	11	13	11,5	4,3	-	8
K0110.003X10	-1.5 - 4.5	0.002	M3	15	11	13	11,5	4,3	-	10
K0110.003X12	-1.5 - 4.5	0.002	M3	15	11	13	11,5	4,3	-	12

Overview of items

Order No.	Thread type	Component material	D	D1	D2	D3	H	H1	T	L
K0110.003X15	-1.5 - 4.5	0.002	M3	15	11	13	11,5	4,3	-	15
K0110.004X8	-1.5 - 4.5	0.002	M4	15	11	13	11,5	4,3	-	8
K0110.004X10	-1.5 - 4.5	0.002	M4	15	11	13	11,5	4,3	-	10
K0110.004X12	-1.5 - 4.5	0.002	M4	15	11	13	11,5	4,3	-	12
K0110.004X15	-1.5 - 4.5	0.002	M4	15	11	13	11,5	4,3	-	15
K0110.005X10	-1.5 - 4.5	0.002	M5	15	11	13	11,5	4,3	-	10
K0110.005X12	-1.5 - 4.5	0.002	M5	15	11	13	11,5	4,3	-	12
K0110.005X15	-1.5 - 4.5	0.002	M5	15	11	13	11,5	4,3	-	15
K0110.005X20	-1.5 - 4.5	0.002	M5	15	11	13	11,5	4,3	-	20
K0110.006X10	-1.5 - 4.5	0.002	M6	15	11	13	11,5	4,3	-	10
K0110.006X15	-1.5 - 4.5	0.002	M6	15	11	13	11,5	4,3	-	15
K0110.006X20	-1.5 - 4.5	0.002	M6	15	11	13	11,5	4,3	-	20
K0110.006X25	-1.5 - 4.5	0.002	M6	15	11	13	11,5	4,3	-	25
K0110.0003X8	-1.5 - 4.5	22012-25061	M3	15	11	13	11,5	4,3	-	8
K0110.0003X10	-1.5 - 4.5	22012-25061	M3	15	11	13	11,5	4,3	-	10
K0110.0003X12	-1.5 - 4.5	22012-25061	M3	15	11	13	11,5	4,3	-	12
K0110.0003X15	-1.5 - 4.5	22012-25061	M3	15	11	13	11,5	4,3	-	15
K0110.0004X8	-1.5 - 4.5	22012-25061	M4	15	11	13	11,5	4,3	-	8
K0110.0004X10	-1.5 - 4.5	22012-25061	M4	15	11	13	11,5	4,3	-	10
K0110.0004X12	-1.5 - 4.5	22012-25061	M4	15	11	13	11,5	4,3	-	12
K0110.0004X15	-1.5 - 4.5	22012-25061	M4	15	11	13	11,5	4,3	-	15
K0110.0005X10	-1.5 - 4.5	22012-25061	M5	15	11	13	11,5	4,3	-	10
K0110.0005X12	-1.5 - 4.5	22012-25061	M5	15	11	13	11,5	4,3	-	12
K0110.0005X15	-1.5 - 4.5	22012-25061	M5	15	11	13	11,5	4,3	-	15
K0110.0005X20	-1.5 - 4.5	22012-25061	M5	15	11	13	11,5	4,3	-	20
K0110.0006X10	-1.5 - 4.5	22012-25061	M6	15	11	13	11,5	4,3	-	10
K0110.0006X15	-1.5 - 4.5	22012-25061	M6	15	11	13	11,5	4,3	-	15
K0110.0006X20	-1.5 - 4.5	22012-25061	M6	15	11	13	11,5	4,3	-	20
K0110.0006X25	-1.5 - 4.5	22012-25061	M6	15	11	13	11,5	4,3	-	25