


Swing clamps pneumatic, Form A

Item description/product images



Description

Material:

Body aluminium.

Double-acting piston rod stainless steel.

Version:

Body black anodised.

Note:

Swing clamps are used where low clamping forces suffice or where the clamping point must be free when mounting and removing the workpiece. The block form of the housing offers universal fastening possibilities. The magnetic piston is primed for electrical end position feedback.

Including screw and lock washer for fastening the clamping arms (accessories).

The swing action of the clamp should not be blocked.

F1 = at 6 bar (max. operating pressure).


On request:

Proximity switch.

Accessory:


- Clamping arm K1816
- Adapter K1817

Examples:



Swing clamps pneumatic, Form A

Drawings



Overview of items

Order No.	Version 2	Form	Size	A	A1	A2	A3	A5	B	D	D1	D2	D3	D4	D5
K1815.1121	pin POM	A	12	35	0	10	31	20	24	8	M5	4,3	M5	M5	4,3
K1815.1161	pin POM	A	16	41	-2	11	31	21	28	8	M5	4,3	M5	M5	4,3
K1815.2121	pin form	A	12	35	0	10	31	20	24	8	M5	4,3	M5	M5	4,3
K1815.2161	pin form	A	16	41	-2	11	31	21	28	8	M5	4,3	M5	M5	4,3

Order No.	H	H1	H2	H3	H4	H5	H6	Travel S	L	S1	S2	T	T1	F1 N
K1815.1121	76	105	70	11	51	26	21	16	40	7	9	5	15	30
K1815.1161	76	105	70	11	51	26	21	16	42	7	9	4,5	15	60
K1815.2121	76	105	70	11	51	26	21	16	40	7	9	5	15	30
K1815.2161	76	105	70	11	51	26	21	16	42	7	9	4,5	15	60