

Clamping pin, steel or stainless steel with adapter plate

Item description/product images



Description

Material:

Adapter plate steel.

Wedges steel 1.0715 or stainless steel 1.4305.

Version:

Adapter plate electro zinc-plated.

Wedges black oxidised or blank.


Note:

The adapter plates enable the toggle clamp to be compatible with hole pattern 3 or 4, for hole grid plates or plates with $\varnothing 16$ mm, $\varnothing 20$ mm or $\varnothing 28$ mm holes.

The clamping pin parts lock in the hole when the cap screw is turned.

Clamping pin, steel or stainless steel with adapter plate

Drawings



Overview of items

Clamping pin, steel or stainless steel with adapter plate

Order No.	Form	Main material	B	B1	B2	B3	B4	D	D1	D2	D3	H	H1	L	L1	L2	L3	L4	L5	L6	L7	L8	S	SW
K1506.0016	A	steel	52	13	26	-	-	16	M5	-	-	30,5	17,5	66	11	30	13	26	-	-	-	-	5	6
K1506.1020	A	stainless steel	52	13	26	-	-	20	M5	-	-	34	21	66	11	30	13	26	-	-	-	-	5	6
K1506.0028	A	steel	52	13	26	-	-	28	M5	-	-	41	28	66	11	30	13	26	-	-	-	-	5	6
K1506.0116	B	steel	52	7	38	-	-	16	M5	M6	-	30,5	17,5	96	11	30	7	38	-	-	-	-	5	6
K1506.1120	B	stainless steel	52	7	38	-	-	20	M5	M6	-	34	21	96	11	30	7	38	-	-	-	-	5	6
K1506.0128	B	steel	52	7	38	-	-	28	M5	M6	-	41	28	96	11	30	7	38	-	-	-	-	5	6
K1506.0216	C	steel	52	13	26	7	38	16	M5	M5	M6	30,5	17,5	96	11	30	13	26	26	7	38	30	5	6
K1506.1220	C	stainless steel	52	13	26	7	38	20	M5	M5	M6	34	21	96	11	30	13	26	26	7	38	30	5	6
K1506.0228	C	steel	52	13	26	7	38	28	M5	M5	M6	41	28	96	11	30	13	26	26	7	38	30	5	6