

Swivel castors with stop fix

Item description/product images



Description

Material:

Housing and wheel rim steel plate.

Tyres solid rubber.

Wheel hub steel tube.

Version:

Housing and rim press formed.

Double ball bearing with ball shield in castor head.


Roller bearings in the wheels.

Note:

Wheel axle bolted.


Drawings

swivel castor
with "stop-fix"



Swivel castors with stop fix

Drawings



Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	L	L1	H	R	Permissible load kg
K1761.080252	Swivel castor	with stop-fix locking system	roller bearing	38	25	-	60	85	80	9	100	80	102	78	50
K1761.100302	Swivel castor	with stop-fix locking system	roller bearing	36	30	-	60	85	100	9	100	80	125	86	70
K1761.125382	Swivel castor	with stop-fix locking system	roller bearing	40	37,5	-	60	85	125	9	100	80	150	102,5	100
K1761.160402	Swivel castor	with stop-fix locking system	roller bearing	60	40	75	80	110	160	11	140	105	195	140	135
K1761.200502	Swivel castor	with stop-fix locking system	roller bearing	65	50	75	80	110	200	11	140	105	235	165	205