


## Quarter-turn clamp lock with recessed grip

### Item description/product images



### Description

#### Material:

Housing and grip stainless steel 1.4310.

Pin stainless steel 1.4305.

#### Version:

Bright.

#### Note:

Stainless steel M2,5 fastening screws are included.

Mounting option 1 for plate thickness 6 mm.

Mounting option 2 for plate thickness >6 mm.

A gap of more than 0.1 mm appears between the plates if the retaining force is exceeded.

#### Type of operation:

Ensure that the twist grip is in the "OFF" position.

Insert the quarter-turn clamp lock into the clamping plate and turn the grip to the 'ON' position.

When fully clamped, an audible click will be heard.

#### Accessory:




Stainless steel clamping plate K2327 for quarter-turn clamp lock with recessed grip.

#### Drawing reference:

- 1) Mounting option 1
- 2) Mounting option 2
- 3) Plate
- 4) Suitable for M 2.5 countersunk head fastening screws

# Quarter-turn clamp lock with recessed grip

## Drawings



## Overview of items

### Quarter-turn clamp lock with recessed grip

Order No.	D	D1	D2	D3	D4	D5	D6	H	H1	H2	M	T	T1	T2
K2326.12813	28	13	39	25	32	39	28	16,5	8,5	2	M02,5	6	>6	3,5

## Quarter-turn clamp lock with recessed grip

### Overview of items

---

Order No.	Shearing force kN	Clamping force N	Pullout force F kN	Holding force N	Temperature resistance
K2326.12813	2,5	30	1	30	≤180 °C