


Shaft collars one-piece, wide, slitted inside

Item description/product images



Description

Material:

Steel.

Stainless steel 1.4305.

Version:

Steel black oxidised.

Screw 12.9 steel.

Stainless steel bright.

Screw A2-70 stainless steel.

Note:

One-piece shaft collars with an inner slit surround the shaft with an equal distribution of the clamping force. This leads to a very precise fit and high retaining force without damaging the shaft.

The shaft tolerance should lie within h11.


Temperature range:

-40 °C - +175 °C.

On request:

Other dimensions.

Drawings



Overview of items

One-piece shaft collars, wide, slitted inside

Order No.	Form definition	Main material	B	C (DIN 912)	D1	D2	R
K1924.00801	Pull-down jaw	0.0035	20	M3x8	8	18	22,4
K1924.01001	Pull-down jaw	0.0035	20	M3x10	10	24	26
K1924.01201	Pull-down jaw	0.0035	24	M4x12	12	28	31,8
K1924.01601	Pull-down jaw	0.0035	29	M5x16	16	34	39,4
K1924.02001	Pull-down jaw	0.0035	33	M6x18	20	40	46,4
K1924.02501	Pull-down jaw	0.0035	33	M6x18	25	45	50,8
K1924.03001	Pull-down jaw	0.0035	33	M6x18	30	54	58,6

Shaft collars one-piece, wide, slitted inside

Overview of items

Order No.	Form definition	Main material	B	C (DIN 912)	D1	D2	R
K1924.04001	Pull-down jaw	0.0035	33	M6x18	40	60	65
K1924.05001	Pull-down jaw	0.0035	41	M8x25	50	78	87
K1924.00802	Pull-down jaw	25	20	M3x8	8	18	22,4
K1924.01002	Pull-down jaw	25	20	M3x10	10	24	26
K1924.01202	Pull-down jaw	25	24	M4x12	12	28	31,8
K1924.01602	Pull-down jaw	25	29	M5x16	16	34	39,4
K1924.02002	Pull-down jaw	25	33	M6x18	20	40	46,4
K1924.02502	Pull-down jaw	25	33	M6x18	25	45	50,8
K1924.03002	Pull-down jaw	25	33	M6x18	30	54	58,6
K1924.04002	Pull-down jaw	25	33	M6x18	40	60	65
K1924.05002	Pull-down jaw	25	41	M8x25	50	78	87