

Crank handles stainless steel with revolving grip

Item description/product images



Description

Version:


Bright.

Note:

Similar to DIN 469.

Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

Drawings



Overview of items

Crank handles stainless steel with cylindrical revolving grip

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L	SW
K0999.3110	Cam-action indexing plungers	DIN 39	80	24	10	16	-	82	60	22	13,4	-	100	-
K0999.3212	Cam-action indexing plungers	DIN 39	100	28	12	20	-	98	72	26	16	-	124	-
K0999.3314	Cam-action indexing plungers	DIN 39	125	30	14	26	-	118	90	28	15,8	-	153	-
K0999.3417	Cam-action indexing plungers	DIN 39	160	34	17	26	-	122	90	32	19,6	-	190	-
K0999.31106	Cam-action indexing plungers	ChromLine clamping joints	80	24	10	16	M6	82	60	22	13,4	7,5	100	-
K0999.32126	Cam-action indexing plungers	ChromLine clamping joints	100	28	12	20	M6	98	72	26	16	7,5	124	-

Crank handles stainless steel with revolving grip

Overview of items

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L	SW
K0999.33146	Cam-action indexing plungers	ChromLine clamping joints	125	30	14	26	M6	118	90	28	15,8	7,5	153	-
K0999.34176	Cam-action indexing plungers	ChromLine clamping joints	160	34	17	26	M6	122	90	32	19,6	7,5	190	-
K0999.4110	Clamping claws	DIN 39	80	24	-	16	-	82	60	22	13,4	-	100	10
K0999.4212	Clamping claws	DIN 39	100	28	-	20	-	98	72	26	16	-	124	12
K0999.4314	Clamping claws	DIN 39	125	30	-	26	-	118	90	28	15,8	-	153	14
K0999.4417	Clamping claws	DIN 39	160	34	-	26	-	122	90	32	19,6	-	190	17
K0999.41106	Clamping claws	ChromLine clamping joints	80	24	-	16	M6	82	60	22	13,4	7,5	100	10
K0999.42126	Clamping claws	ChromLine clamping joints	100	28	-	20	M6	98	72	26	16	7,5	124	12
K0999.43146	Clamping claws	ChromLine clamping joints	125	30	-	26	M6	118	90	28	15,8	7,5	153	14
K0999.44176	Clamping claws	ChromLine clamping joints	160	34	-	26	M6	122	90	32	19,6	7,5	190	17