



HEINRICH KIPP WERK



# WORKPIECE stabiliser

Edition 06 2023



# CONTENTS



+49 7454 793-0



+49 7454 793-7982



sales@kipp.com



www.kipp.com

---

## WORKPIECE-STABILISER

Product overview	5
Technical information	6-7

---

## PRODUCTS

Workpiece stabiliser set with case	8
Workpiece stabiliser	9
Extension shafts for workpiece stabiliser	9
Fine adjustment for workpiece stabiliser	10
Magnet for workpiece stabiliser	11
Fastening set for T-slot workpiece stabiliser	12
Fastening set for Zero Point	
Clamping Technology workpiece stabiliser	12
Claw clamp for workpiece stabiliser	13
Clamping balls with cup for workpiece stabiliser	14

---



Per. № 002081qm15



## SERVICE-HOURS (CET)

MONDAY - THURSDAY	7.00 am - 5.30 pm
FRIDAY	7.00 am - 3.30 pm





## Workpiece stabiliser



Workpiece stabiliser set  
with case  
**K1296**



Seite 8

Workpiece stabiliser  
**K1170**



Seite 9

Extension shafts  
for workpiece stabiliser  
**K1186**



Seite 9

Fine adjustment  
for workpiece stabiliser  
**K1187**



Seite 10

Magnet  
for workpiece stabiliser  
**K1188**



Seite 11

Fastening set for T-slot  
workpiece stabiliser  
**K1189**



Seite 12

Fastening set for Zero Point Clamping  
Technology  
workpiece stabiliser  
**K1190**



Seite 12

Claw clamp  
for workpiece stabiliser  
**K1192**



Seite 13

Clamping balls with cup  
for workpiece stabiliser  
**K1193**



Seite 14

# Technical information Workpiece stabiliser



The workpiece stabiliser has been developed specifically for minimising vibrations and oscillations when machining sensitive and thin-walled workpieces.

This system is extremely flexible thanks to its different methods of fixing to the workpiece and the machine table.





- 1 Fastening set for T-slots
- 2 Magnet
- 3 Fastening set for zero-point interface
- 4 Workpiece stabiliser
- 5 Fine adjustment
- 6 Clamp strap
- 7 Clamping ball with cup

# Workpiece stabiliser set

with case



**Material:**

Case plastic.

See corresponding product group for contents.

**Version:**

black.

**Sample order:**

K1296.925

**Note:**

Objects sized between 355 and 980 mm can be set up using this stabiliser set.

It is basic equipment for supporting workpieces.

The individual parts are safely stored in a plastic case.

The length of the workpiece stabiliser is infinitely adjustable.

With the locking mechanism, the shaft can be securely locked against tension and compression.


**Supplied with:**

- Case
- Workpiece stabiliser, K1170.355505
- Extension shaft L75, K1186.1625075
- Extension shaft L100, K1186.1625100
- Extension shaft L150, K1186.1625150
- Precision adjustment, K1187.25120150
- Fastening set for T-slots, 14 mm T-slot set, K1189.2514
- 18 mm T-slot block with M10, K0378.18.005
- 22 mm T-slot block with M10, K0378.22.005
- Clamping ball with cup M12, K1193.3251240
- Clamping ball with cup M16, K1193.3251640

## KIPP Workpiece stabiliser set with case

Order No.	Item	Version 1
K1296.925	Workpiece Stabiliser Set	with case

## Workpiece stabiliser




**Material:**  
Steel.

**Version:**  
Telescopic clamping unit and fastening set black oxidised.  
Shaft bright.

**Sample order:**  
K1170.255305

**Note:**  
The length of the workpiece stabiliser is infinitely adjustable. The shaft can be securely clamped against tension and thrust by means of a locking mechanism.

The workpiece stabiliser consists of a telescopic clamping unit with two fastening sets and two clamping balls with Form B cups for system sizes 25 or 50.




Order No.	Size	L min.	L max.	weight kg
K1170.255305	25	255	305	1,9
K1170.355505	25	355	505	2,5
K1170.50350450	50	350	450	6,7
K1170.50450650	50	450	650	7,7

# K1186

## Extension shafts

for workpiece stabiliser



**Material:**  
Steel.

**Sample order:**  
K1186.1625075

**Note:**  
The extension shafts extend the adjustment range. They are mounted with the clamping ball between the workpiece stabiliser and the fastening set.

### KIPP Extension shafts for workpiece stabiliser


Order No.	Size	D	D1	L	SW	weight kg
K1186.1625075	25	M16x1,5	25	75	21	0,233
K1186.1625100	25	M16x1,5	25	100	21	0,293
K1186.1625150	25	M16x1,5	25	150	21	0,416
K1186.1625250	25	M16x1,5	25	250	21	0,697
K1186.1625500	25	M16x1,5	25	500	21	1,3
K1186.2750100	50	M27x2	40	100	36	0,726
K1186.2750150	50	M27x2	40	150	36	1,04
K1186.2750250	50	M27x2	40	250	36	1,623
K1186.2750500	50	M27x2	40	500	36	3,12

## Fine adjustment


for workpiece stabiliser



System size 25



Adapter for system size 50



The fine adjustment enables the distance between the workpiece and support table to be precisely set. If required, the fine adjustment can be used to set the workpiece stabiliser under tensile or compressive load.

**Material:**  
Steel.

**Version:**  
Adapter piece black oxidised.  
Half shells nitrided.

**Sample order:**  
K1187.25120150

**Note:**  
Only the fine adjuster K1187.25120150 is required for workpiece stabiliser system size 25.

When using fine adjustment on the workpiece stabiliser system size 50, the fine adjuster K1187.25120150 and the adapter K1187.50 (consisting of 2 adapter pieces and a grub screw) are required at the respective ends.

**Drawing reference:**  
1) DIN EN ISO 4762 M10 cap screw

### KIPP Fine adjustment for workpiece stabiliser


Order No.	Item	Size	B	D	D1	D2	H	L	L	L	L1	L2	SW
								min.	max.				
K1187.25120150	Fine Adjustment	25	44	25	M16x1,5	9	46	120	150	-	16	-	21
K1187.50	Adapter	50	-	39,7	M16x1,5	M27x2	-	-	-	38	34	35	36

## Magnet


for workpiece stabiliser



System size 25



System size 50



The magnet is connected to the workpiece stabiliser. The magnet can be positioned anywhere enabling flexible placement on the machine table.

**Sample order:**  
K1188.25161064

**Note:**

Maximum hold with the magnet K1188.25161064 for workpiece stabiliser system size 25 is achieved with a material thickness from 8 mm.

Maximum hold with the magnet K1188.50205087 for workpiece stabiliser system size 50 is achieved with a material thickness from 15 mm.

Must not be used as a hoisting tool.

The clamping balls can be exchanged between the two system sizes by using the matching adapter plates.


### KIPP Magnet for workpiece stabiliser

Order No.	Size	B	H	H1	H2	L	L1	L2	Magnetic force N	weight kg
K1188.25161064	25	64	60	102	133	161	122	92	1470	3,73
K1188.50205087	50	87	78	134	181	205	162	145	1960	8,6


## Fastening set for T-slot

workpiece stabiliser

System size 25



System size 50



**Material:**  
Steel.

**Sample order:**  
K1189.2512

**Note:**  
These fastening sets for T-slots are for adapting to machine tables with T-slots.

The clamping balls can be exchanged between the two system sizes.


Order No.	Size	B	D	D1	D2	H	H1
K1189.2514	25	14	25,4	M10	78	10	35
K1189.2518	25	18	25,4	M10	78	10	35
K1189.2522	25	22	25,4	M10	78	10	35
K1189.2528	25	28	25,4	M10	78	10	35
K1189.5014	50	14	50	M10	78	10	30
K1189.5018	50	18	50	M10	78	10	30
K1189.5022	50	22	50	M10	78	10	30
K1189.5028	50	28	50	M10	78	10	30

# K1190


## Fastening set for Zero Point Clamping Technology

workpiece stabiliser

System size 25



System size 50



**Material:**  
Steel.

**Sample order:**  
K1190.2540

**Note:**  
The fastening set is suitable for adaption to UNILOCK zero point clamping technology.


The clamping balls can be exchanged between the two system sizes.

### KIPP Fastening set for Zero Point Clamping Technology workpiece stabiliser

Order No.	Size	D	D1	H	H1
K1190.2540	25	25,4	78	10	35
K1190.5040	50	50	78	10	30

## Claw clamp

for workpiece stabiliser



**Material:**  
Steel.

**Version:**  
Claw clamps black oxidised.  
Clamping ball bright.

**Sample order:**  
K1192.258076


**Note:**  
The clamping unit is used for connecting to the workpiece. The clamping ball can be attached to several points on the claw clamp. This enables flexible adjustment of the claw clamp.

### KIPP Clamp strap for workpiece stabiliser

Order No.	Size	B	B1	D	G	H clamping range	H1	L	L1	L2	L3
K1192.258076	25	64	79	25,4	M16	0-45	27	25	25	76	66
K1192.508076	50	64	79	50	M16	0-45	27	20	25	76	66


The clamping balls can be exchanged between the two system sizes.

## Notes



## Clamping balls with cup

for workpiece stabiliser



**Material:**  
Steel.

**Version:**  
DIN EN ISO 4017 hex head bolt , grade 8.8, black.  
DIN EN ISO 4762 cap screw grade 8.8, black.  
Clamping ball bright.

**Sample order:**  
K1193.125

**Note:**  
The clamping balls enable flexible connections between the workpiece and the workpiece stabiliser. The clamping balls provide a high degree of freedom on the workpiece.

**Drawing reference:**  
1) DIN EN ISO 4762 cap screw

### KIPP Clamping balls with cup for workpiece stabiliser

Order No.	Form	Size	D	D1	D2	D3	L	L1	L2	SW
K1193.125	A	25	25,4	M10	29	18	25	12,2	4,5	-
K1193.225	B	25	25,4	M10	29	-	25	11	-	-
K1193.250	B	50	50	M16	49	-	30	20,5	-	-
K1193.3251240	C	25	25,4	M12	-	-	17,3	40	-	18
K1193.3251640	C	25	25,4	M16	-	-	19,8	40	-	24
K1193.3252050	C	25	25,4	M20	-	-	22,3	50	-	30
K1193.3252450	C	25	25,4	M24	-	-	24,8	50	-	36
K1193.3502450	C	50	50	M24	-	-	34,5	50	-	36
K1193.3503060	C	50	50	M30	-	-	34,5	60	-	46
K1193.3503670	C	50	50	M36	-	-	34,5	70	-	55
K1193.450	D	50	50	M16	25	-	20	18	3,5	-



The standard terms and conditions of sale, delivery and payment that you can find on our website [www.kipp.com](http://www.kipp.com) apply.

**HEINRICH KIPP WERK GmbH & Co. KG**

Heubergstraße 2  
72172 Sulz am Neckar

Tel. +49 7454 793-7652  
Fax +49 7454 793-7983  
E-Mail [spanntechnik@kipp.com](mailto:spanntechnik@kipp.com)  
Internet [www.kipp.com](http://www.kipp.com)

HEINRICH KIPP WERK GmbH & Co. KG

Heubergstraße 2

72172 Sulz am Neckar

GERMANY

Tel. +49 7454 793-0

[info@kipp.com](mailto:info@kipp.com)

[www.kipp.com](http://www.kipp.com)



WE01ENPR2306